



SVN411

~ ~ ~ ~ ~

~ ~ ~ ~ ~

**Impulse 1NO Pushbutton + green Indicator light 230VAC**

**Technical characteristics**

**Main electrical features**

Rated operational voltage Ue	230 V
Frequency	50/60 Hz

**Voltage**

Rated insulation voltage	250 V
Rated impulse withstand voltage	4000 V

**Dimensions**

Depth of installed product	66 mm
Height of installed product	83 mm
Width of installed product	17.5 mm

**Power**

Total power loss under IN	0.8 W
---------------------------	-------

**Endurance**

Electric endurance in number of cycles	15000
Number of mechanical operations	15000

**Materials**

Colour	green
--------	-------

**Lighting control**

Type of lamp	LED
--------------	-----

**Installation, mounting**

Tightening torque	1,7Nm
-------------------	-------

**Connection**

Connection cross-sect. flexible conductor	0,75 / 6mm <sup>2</sup>
Connection cross-sect. rigid cable	0,75 / 10mm <sup>2</sup>
Type of connection	with screw

**Standards**

European directive WEEE	concerned
-------------------------	-----------

**Safety**

Protection index IP	IP20
---------------------	------

**Use conditions**

Operating temperature	-20...50 °C
-----------------------	-------------