



SVN413



Latching 1NO Pushbutton + green Indicator light 230VAC

Technical characteristics

Main electrical features

| | |
|------------------------------|----------|
| Rated operational voltage Ue | 230 V |
| Frequency | 50/60 Hz |

Voltage

| | |
|---------------------------------|--------|
| Rated insulation voltage | 250 V |
| Rated impulse withstand voltage | 4000 V |

Dimensions

| | |
|-----------------------------|---------|
| Depth of installed product | 66 mm |
| Height of installed product | 83 mm |
| Width of installed product | 17.5 mm |

Power

| | |
|---------------------------|-------|
| Total power loss under IN | 0.8 W |
|---------------------------|-------|

Endurance

| | |
|--|-------|
| Electric endurance in number of cycles | 15000 |
| Number of mechanical operations | 15000 |

Materials

| | |
|--------|-------|
| Colour | green |
|--------|-------|

Lighting control

| | |
|--------------|-----|
| Type of lamp | LED |
|--------------|-----|

Standards

| | |
|-------------------------|-----------|
| European directive WEEE | concerned |
|-------------------------|-----------|

Safety

| | |
|---------------------|------|
| Protection index IP | IP20 |
|---------------------|------|

Use conditions

| | |
|-----------------------|-------------|
| Operating temperature | -20...50 °C |
|-----------------------|-------------|