



SVN433



## Latching 2NO Pushbutton + green Indicator light 230VAC

### Technical characteristics

#### Main electrical features

Rated operational voltage U <sub>e</sub>	230 V
Frequency	50/60 Hz

#### Voltage

Rated insulation voltage	250 V
Rated impulse withstand voltage	4000 V

#### Dimensions

Depth of installed product	66 mm
Height of installed product	83 mm
Width of installed product	17.5 mm

#### Power

Total power loss under I <sub>N</sub>	0.8 W
---------------------------------------	-------

#### Endurance

Electric endurance in number of cycles	15000
Number of mechanical operations	15000

#### Materials

Colour	green
--------	-------

#### Lighting control

Type of lamp	LED
--------------	-----

#### Installation, mounting

Tightening torque	1,7Nm
-------------------	-------

#### Connection

Type of connection	with screw
--------------------	------------

#### Safety

Protection index IP	IP20
---------------------	------

#### Use conditions

Operating temperature	-20...50 °C
-----------------------	-------------