



SVN433



**Latching 2NO Pushbutton + green Indicator light 230VAC**

**Technical Characteristics**

Rated operational voltage Ue	230 V
Frequency	50/60 Hz
Rated current	16 A
Rated insulation voltage	250 V
Rated impulse withstand voltage	4000 V
Depth of installed product	66 mm
Height of installed product	83 mm
Width of installed product	17.5 mm
Total power loss under IN	0.8 W
Electric endurance in number of cycles	15000
Number of mechanical operations	15000
Number of modules	1
Colour	green
Type of lamp	LED
Tightening torque	1,7Nm
Connection cross-sect. flexible conductor	0,75 / 6mm <sup>2</sup>
Connection cross-sect. rigid cable	0,75 / 10mm <sup>2</sup>
Type of connection	with screw
Can be accessorized	No
European directive WEEE	concerned
Protection index IP	IP20
Operating temperature	-20...50 °C