



TE360

IP20

3Ph Kwhmeter direct 100A with KNX output

Technical characteristics

Architecture

Bus system KNX

Connectivity

Bus system radio frequent No

Main electrical features

Frequency 50/60 Hz

Power

Total power loss under IN 2 W

Connection

Type of connection with screw terminals

Equipment

Type of counter other

Safety

Protection index IP IP20

Use conditions

Operating temperature -10...55 °C