



TJA450

domovea Softwarelösung (Server + Client) mit USB/KNX Interface

Technical characteristics

Architecture

Fixing mode REG

Controls and indicators

Indicator lamp yes

Connectivity

Bus system radio frequent No

Power

Total power loss under IN 3.9 W

Materials

Colour stone grey

RAL colour RAL 7035 - Light grey

Material other

Material plastic

Type of surface treatment untreated

Accessories included

Inscribable, with labelling field Yes

Safety

Protection index IP IP20

Use conditions

Operating temperature 0...45 °C