



TR302A

2 flush mounted battery inputs

Technical characteristics

Architecture

Fixing mode	flush-mounting
-------------	----------------

Controls and indicators

Indicator lamp	lighting indicator
----------------	--------------------

Dimensions

Dimensions (LLxwwxhh)	48 x 53 x 30 mm
-----------------------	-----------------

Power

Total power loss under IN	0.4 W
---------------------------	-------

Reach distance

Max. transmission range	30m in house / 100m free field
-------------------------	--------------------------------

Materials

Colour	stone grey
--------	------------

Use conditions

Operating temperature	0...45 °C
-----------------------	-----------