



TR302B

2 flush mounted inputs mains powered

Technical characteristics

Architecture

Fixing mode flush-mounting

Controls and indicators

Indicator lamp yes

Dimensions

Dimensions (LLxwwxhh) 48 x 53 x 30 mm

Power

Total power loss under IN 0.9 W

Materials

Colour stone grey

Safety

Protection index IP IP20

Use conditions

Operating temperature 0...45 °C