



TR304A

4 flush mounted battery inputs

Technical characteristics

Architecture

Fixing mode flush-mounting

Controls and indicators

Indicator lamp lighting indicator

Dimensions

Dimensions (LLxwwxhh) 48 x 53 x 30 mm

Reach distance

Max. transmission range 30m in house / 100m free field

Materials

Colour stone grey

Use conditions

Operating temperature 0...45 °C