



TR304B

**4 flush mounted inputs mains powered**

**Technical characteristics**

**Architecture**

|             |                |
|-------------|----------------|
| Fixing mode | flush-mounting |
|-------------|----------------|

**Controls and indicators**

|                |     |
|----------------|-----|
| Indicator lamp | yes |
|----------------|-----|

**Dimensions**

|                       |                 |
|-----------------------|-----------------|
| Dimensions (LLxwwxhh) | 48 x 53 x 30 mm |
|-----------------------|-----------------|

**Power**

|                           |     |
|---------------------------|-----|
| Total power loss under IN | 1 W |
|---------------------------|-----|

**Reach distance**

|                         |                                |
|-------------------------|--------------------------------|
| Max. transmission range | 30m in house / 100m free field |
|-------------------------|--------------------------------|

**Materials**

|        |            |
|--------|------------|
| Colour | stone grey |
|--------|------------|

**Safety**

|                     |      |
|---------------------|------|
| Protection index IP | IP20 |
|---------------------|------|

**Use conditions**

|                       |           |
|-----------------------|-----------|
| Operating temperature | 0...45 °C |
|-----------------------|-----------|