



TRB201



Module 1 output 16A flush mounted KNX

Technical characteristics

Architecture

Bus system	KNX
Fixing mode	flush-mounting

Functions

Function	reset function (to factory setting)
----------	-------------------------------------

Controls and indicators

Indicator lamp	yes
----------------	-----

Connectivity

Bus system radio frequent	Yes
---------------------------	-----

Main electrical features

Frequency	50/60 Hz
-----------	----------

Dimensions

Height	30 mm
Dimensions (LLxwxh)	48 x 53 x 30 mm

Power

Power consumed	3 VA
Total power loss under IN	2 W

Materials

Surface appearance	matt
--------------------	------

Incandescent bulbs control

Max. power with incandescent lamps	2300 W
------------------------------------	--------

Connection

Connection cross-sect. flexible conductor	2,5mm ²
Connection cross-sect. rigid cable	2,5mm ²
Type of contacts	1NO
Type of connection	with screw-in lift terminals

Use conditions

Operating temperature	0...45 °C
-----------------------	-----------