



TRB210



1 flush mounted dimming output 200W

Technical characteristics

Architecture

Fixing mode	flush-mounting
-------------	----------------

Controls and indicators

Indicator lamp	yes
----------------	-----

Main electrical features

Frequency	50 Hz
-----------	-------

Voltage

Operating voltage	230 V AC
-------------------	----------

Fuse

Fuse	short-circuit and overload proof (electronic fuse)
------	--

Power

Incandescent bulb power	20 / 200 W
-------------------------	------------

Materials

Colour	light grey
--------	------------

Connection

Type of load	universal
Type of connection	with screw-in lift terminals

Equipment

Dimming principle	phase cut-on or cut-off according to load type, self-learning
-------------------	---

Safety

Protection index IP	IP30
---------------------	------

Use conditions

Operating temperature	0...45 °C
-----------------------	-----------