



TRB302A



2 flush mounted battery inputs

Technical characteristics

Architecture

Fixing mode flush-mounting

Voltage

Operating voltage 3 V DC

Dimensions

Dimensions (LLxwwxhh) 48 x 53 x 30 mm

Power

Total power loss under IN 0.4 W

Materials

Colour stone grey

RAL colour RAL 7035 - Light grey

Safety

Protection index IP IP30

Use conditions

Operating temperature 0...45 °C