



TRB302A



2 flush mounted battery inputs

Technical characteristics

Functions

Function	reset function (to factory setting) ; easy additional functions: +6 scenes, on/off operating mode, 1 up/down button control
----------	---

Controls and indicators

Indicator lamp	lighting indicator
----------------	--------------------

Voltage

Operating voltage	3 V DC
-------------------	--------

Dimensions

Dimensions (LLxwxh)	48 x 53 x 30 mm
---------------------	-----------------

Power

Total power loss under IN	0.4 W
---------------------------	-------

Reach distance

Max. transmission range	30m in house / 100m free field
-------------------------	--------------------------------

Materials

RAL colour	RAL 7035 - Light grey
------------	-----------------------

Installation, mounting

Mounting type	flush
---------------	-------

Connection

Connection cross-sect. flexible conductor	0,5 / 2,5mm ²
Connection cross-sect. rigid cable	0,5 / 2,5mm ²

Use conditions

Operating temperature	0...45 °C
-----------------------	-----------