



TRB302A



## 2 flush mounted battery inputs

### Technical characteristics

#### Functions

|          |   |
|----------|---|
| Function | reset function (to factory setting) ; easy additional functions: +6 scenes, on/off operating mode, 1 up/down button control |
|----------|---|

#### Controls and indicators

|                |                    |
|----------------|--------------------|
| Indicator lamp | lighting indicator |
|----------------|--------------------|

#### Voltage

|                   |        |
|-------------------|--------|
| Operating voltage | 3 V DC |
|-------------------|--------|

#### Dimensions

|                      |                 |
|----------------------|-----------------|
| Dimensions (LLxwxhh) | 48 x 53 x 30 mm |
|----------------------|-----------------|

#### Power

|                           |       |
|---------------------------|-------|
| Total power loss under IN | 0.4 W |
|---------------------------|-------|

#### Reach distance

|                         |                                |
|-------------------------|--------------------------------|
| Max. transmission range | 30m in house / 100m free field |
|-------------------------|--------------------------------|

#### Materials

|            |                       |
|------------|-----------------------|
| RAL colour | RAL 7035 - Light grey |
|------------|-----------------------|

#### Installation, mounting

|               |       |
|---------------|-------|
| Mounting type | flush |
|---------------|-------|

#### Connection

|   |                          |
|---|--------------------------|
| Connection cross-sect. flexible conductor | 0,5 / 2,5mm <sup>2</sup> |
| Connection cross-sect. rigid cable        | 0,5 / 2,5mm <sup>2</sup> |

#### Use conditions

|                       |           |
|-----------------------|-----------|
| Operating temperature | 0...45 °C |
|-----------------------|-----------|