



TRB302A



2 flush mounted battery inputs

Technical characteristics

Architecture

Fixing mode	flush-mounting
-------------	----------------

Functions

Function	reset function (to factory setting), easy additional functions: +6 scenes, on/off operating mode, 1 up/down button control
----------	----------------------------------------------------------------------------------------------------------------------------

Voltage

Operating voltage	3 V DC
-------------------	--------

Dimensions

Dimensions (LLxwwxhh)	48 x 53 x 30 mm
-----------------------	-----------------

Power

Total power loss under IN	0.4 W
---------------------------	-------

Materials

Colour	stone grey
RAL colour	RAL 7035 - Light grey

Safety

Protection index IP	IP30
---------------------	------

Use conditions

Operating temperature	0...45 °C
-----------------------	-----------