



TRB302B



Module 2 inputs flush mounted 230V KNX QL

Technical characteristics

Functions

Function	reset function (to factory setting) ; easy additional functions: +6 scenes, on/off operating mode, 1 up/down button control
----------	---

Controls and indicators

Indicator lamp	yes
----------------	-----

Main electrical features

Frequency	50/60 Hz
-----------	----------

Voltage

Operating voltage	230 V AC
-------------------	----------

Dimensions

Dimensions (LLxwwxhh)	48 x 53 x 30 mm
-----------------------	-----------------

Power

Total power loss under IN	0.9 W
---------------------------	-------

Reach distance

Max. transmission range	30m in house / 100m free field
-------------------------	--------------------------------

Materials

RAL colour	RAL 7035 - Light grey
------------	-----------------------

Installation, mounting

Mounting type	flush
---------------	-------

Connection

Connection cross-sect. flexible conductor	0,5 / 2,5mm ²
Connection cross-sect. rigid cable	0,5 / 2,5mm ²
Type of connection	with screw-in lift terminals

Use conditions

Operating temperature	-5...45 °C
-----------------------	------------