



TRB302B



2 flush mounted inputs mains powered

Technical characteristics

Architecture

Fixing mode flush-mounting

Controls and indicators

Indicator lamp yes

Main electrical features

Frequency 50/60 Hz

Voltage

Operating voltage 230 V AC

Dimensions

Dimensions (LLxwwxhh) 48 x 53 x 30 mm

Power

Total power loss under IN 0.9 W

Materials

Colour stone grey

RAL colour RAL 7035 - Light grey

Connection

Type of connection with screw-in lift terminals

Safety

Protection index IP IP20

Use conditions

Operating temperature -5...45 °C