



TRB501



1 flush mounted output 10A + 1 binary input

Technical characteristics

Architecture

Bus system	KNX
Number of blinds/shutters outputs	0
Fixing mode	flush-mounting

Controls and indicators

Indicator lamp	yes
----------------	-----

Connectivity

Bus system radio frequent	Yes
---------------------------	-----

Main electrical features

Rated operational voltage Ue	195 / 230 / 253 V
Frequency	50 Hz
Type of supply voltage	AC

Voltage

Operating voltage	230 V AC
-------------------	----------

Connection

Type of connection	with screw-in lift terminals
--------------------	------------------------------

Equipment

Number of channels	1
--------------------	---

Safety

Protection index IP	IP30
---------------------	------

Use conditions

Operating temperature	0...45 °C
-----------------------	-----------