



TRM600



IP20

quicklink

Control for latching relay, timer KNX radio

Technical characteristics

Functions

Function	pulse function only ; reset function (to factory setting)
----------	-----------------------------------------------------------

Controls and indicators

Indicator lamp	yes
----------------	-----

Connectivity

Bus system radio frequent	Yes
---------------------------	-----

Main electrical features

Frequency	50/60 Hz
-----------	----------

Dimensions

Height	18 mm
Height of installed product	40 mm
Dimensions (LLxwxh)	40x40x18

Power

Total power loss under IN	150 mW
Power dissipation per coil	100 mW

Materials

Surface appearance	matt
--------------------	------

Connection

Connection cross-sect. flexible conductor	0,5 / 1,5mm ²
Connection cross-sect. rigid cable	0,5 / 2,5mm ²
Type of connection	with screw
Type of contacts	semi-conductor
Type of connection	with screw-in lift terminals

Use conditions

Operating temperature	-15...45 °C
-----------------------	-------------