



TRM600



IP20

Control for latching relay, timer KNX radio

Technical characteristics

Architecture

Fixing mode	flush-mounting
-------------	----------------

Controls and indicators

Indicator lamp	yes
----------------	-----

Connectivity

Bus system radio frequent	Yes
---------------------------	-----

Main electrical features

Frequency	50/60 Hz
-----------	----------

Dimensions

Height	18 mm
Height of installed product	40 mm
Dimensions (LLxwxh)	40x40x18

Power

Total power loss under IN	150 mW
Power dissipation per coil	100 mW

Materials

Surface appearance	matt
--------------------	------

Connection

Type of connection	with screw
Type of connection	with screw-in lift terminals

Use conditions

Operating temperature	-15...45 °C
-----------------------	-------------