



TRM690G



IP20

quicklink

Module 1 flush mounted output 200W, 2 wires + 2 inputs, KNX radio

Technical characteristics

Architecture

Bus system KNX

Controls and indicators

Indicator lamp yes

Connectivity

Bus system radio frequent No

Dimensions

Height 18 mm

Height of installed product 40 mm

Dimensions (LLxwwxhh) 40x40x18

Materials

Surface appearance matt

Incandescent bulbs control

Max. power with incandescent lamps 200 W

Connection

Type of connection with screw-in lift terminals

Use conditions

Operating temperature -15...45 °C