



TRM690G



IP20

## Module 1 flush mounted output 200W, 2 wires + 2 inputs, KNX radio

### Technical characteristics

#### Architecture

Bus system KNX

#### Functions

Function reset function (to factory setting) ; easy additional functions: +6 scenes

#### Controls and indicators

Indicator lamp yes

#### Connectivity

Bus system radio frequent No

#### Dimensions

Height 18 mm

Height of installed product 40 mm

Dimensions (LLxwwxhh) 40x40x18

#### Reach distance

Max. transmission range 30m in house / 100m free field

#### Materials

Surface appearance matt

#### Incandescent bulbs control

Max. power with incandescent lamps 200 W

#### Connection

Connection cross-sect. flexible conductor 0,5 / 1,5mm<sup>2</sup>

Connection cross-sect. rigid cable 0,5 / 2,5mm<sup>2</sup>

Type of connection with screw

Type of contacts semi-conductor

Type of connection with screw-in lift terminals

#### Use conditions

Operating temperature -15...45 °C