



TRM690G



IP20

Module 1 flush mounted output 200W, 2 wires + 2 inputs, KNX radio

Technical characteristics

Architecture

Bus system KNX

Functions

Function reset function (to factory setting) ; easy additional functions: +6 scenes

Controls and indicators

Indicator lamp yes

Connectivity

Bus system radio frequent No

Dimensions

Height 18 mm

Height of installed product 40 mm

Dimensions (LLxwxh) 40x40x18

Reach distance

Max. transmission range 30m in house / 100m free field

Materials

Surface appearance matt

Incandescent bulbs control

Max. power with incandescent lamps 200 W

Connection

Connection cross-sect. flexible conductor 0,5 / 1,5mm²

Connection cross-sect. rigid cable 0,5 / 2,5mm²

Type of connection with screw

Type of contacts semi-conductor

Type of connection with screw-in lift terminals

Use conditions

Operating temperature -15...45 °C