



TRM691E



IP20

quicklink

## Module 1 flush mounted dimmer 200W, 2 wires + 2 inputs, KNX radio

### Technical characteristics

#### Functions

Function	reset function (to factory setting)
----------	-------------------------------------

#### Controls and indicators

Indicator lamp	yes
----------------	-----

#### Connectivity

Bus system radio frequent	Yes
---------------------------	-----

#### Fuse

Fuse	short-circuit and overload proof (electronic fuse)
------	--

#### Dimensions

Height	38 mm
--------	-------

#### Power

Incandescent bulb power	10 / 200 W
-------------------------	------------

#### Incandescent bulbs control

Max. power with incandescent lamps	200 W
------------------------------------	-------

#### Connection

Connection cross-sect. flexible conductor	0,5 / 1,5mm <sup>2</sup>
Connection cross-sect. rigid cable	0,5 / 2,5mm <sup>2</sup>
Type of load	universal
Number of contacts	1
Type of connection	with screw-in lift terminals

#### Equipment

Dimming principle	phase cut-on or cut-off according to load type, self-learning
-------------------	---

#### Use conditions

Operating temperature	-15...45 °C
-----------------------	-------------