



TRM691E



IP20

quicklink

**Module 1 flush mounted dimmer 200W, 2 wires + 2 inputs, KNX radio**

**Technical characteristics**

**Controls and indicators**

Indicator lamp yes

**Connectivity**

Bus system radio frequent Yes

**Fuse**

Fuse short-circuit and overload proof (electronic fuse)

**Dimensions**

Height 38 mm

**Power**

Incandescent bulb power 10 / 200 W

**Incandescent bulbs control**

Max. power with incandescent lamps 200 W

**Connection**

Type of load universal

Number of contacts 1

Type of connection with screw-in lift terminals

**Equipment**

Dimming principle phase cut-on or cut-off according to load type, self-learning

**Use conditions**

Operating temperature -15...45 °C