



TRM692G



IK04 IP20

quicklink

Module 1 flush mounted output 3A for shutters or blinds + 2 inputs, KNX radio

Technical characteristics

Architecture

Bus system	KNX
Number of blinds/shutters outputs	1

Functions

Function	easy additional functions: +6 scenes ; reset function (to factory setting) ; Repeat function can be activated to increase the radio range
----------	---

Configuration

Switch mode	with 2 mechanically and electrically mutually-locked relay contacts
-------------	---

Controls and indicators

Indicator lamp	yes
----------------	-----

Connectivity

Bus system radio frequent	Yes
---------------------------	-----

Main electrical features

Frequency	50 Hz
Type of supply voltage	AC

Power

Contact rating with 230 V in AC1	690 W
Total power loss under IN	450 mW
Power dissipation per coil	150 mW

Connection

Connection cross-sect. flexible conductor	0,5 / 1,5mm ²
Connection cross-sect. rigid cable	0,5 / 2,5mm ²
Type of connection	with screw
Number of contacts	1
Type of connection	with screw-in lift terminals

Use conditions

Operating temperature	-10...50 °C
-----------------------	-------------