



TRM693G



IK04 IP20

Module 1 flush mounted output 3A 230V + 2 inputs mains powered, KNX radio

Technical characteristics

Functions

Function	reset function (to factory setting) ; Repeat function can be activated to increase the radio range ; easy additional functions: +6 scenes
----------	---

Controls and indicators

Indicator lamp	yes
----------------	-----

Connectivity

Bus system radio frequent	No
---------------------------	----

Dimensions

Height	20 mm
Height of installed product	40 mm
Dimensions (LLxwxh)	40x40x20

Power

Total power loss under IN	450 mW
Power dissipation per coil	150 mW

Reach distance

Max. transmission range	30m in house / 100m free field
-------------------------	--------------------------------

Materials

Surface appearance	matt
--------------------	------

Fluorescent bulbs control

Max. power fluo. duo lamp comp. series	150W
--	------

Incandescent bulbs control

Max. power with incandescent lamps	500 W
------------------------------------	-------

Connection

Connection cross-sect. flexible conductor	0,5 / 1,5mm ²
Connection cross-sect. rigid cable	0,5 / 2,5mm ²
Type of contacts	1NO
Type of connection	with screw-in lift terminals

Use conditions

Operating temperature	-10...50 °C
-----------------------	-------------