



TRM693G



IK04 IP20

quicklink

## Module 1 flush mounted output 3A 230V + 2 inputs mains powered, KNX radio

### Technical characteristics

#### Functions

Function	reset function (to factory setting) ; Repeat function can be activated to increase the radio range ; easy additional functions: +6 scenes
----------	---

#### Controls and indicators

Indicator lamp	yes
----------------	-----

#### Connectivity

Bus system radio frequent	No
---------------------------	----

#### Dimensions

Height	20 mm
Height of installed product	40 mm
Dimensions (LLxwxh)	40x40x20

#### Power

Total power loss under IN	450 mW
Power dissipation per coil	150 mW

#### Reach distance

Max. transmission range	30m in house / 100m free field
-------------------------	--------------------------------

#### Materials

Surface appearance	mat
--------------------	-----

#### Fluorescent bulbs control

Max. power fluo. duo lamp comp. series	150W
--	------

#### Incandescent bulbs control

Max. power with incandescent lamps	500 W
------------------------------------	-------

#### Connection

Connection cross-sect. flexible conductor	0,5 / 1,5mm <sup>2</sup>
Connection cross-sect. rigid cable	0,5 / 2,5mm <sup>2</sup>
Type of connection	with screw
Type of contacts	1NO
Type of connection	with screw-in lift terminals

#### Use conditions

Operating temperature	-10...50 °C
-----------------------	-------------