



TRM694G



IK04 IP20

quicklink

Module 1 FM output 4A free of potential + 2 inputs mains powered, KNX radio

Technical characteristics

Controls and indicators

Indicator lamp yes

Connectivity

Bus system radio frequent No

Dimensions

Height 20 mm

Height of installed product 40 mm

Dimensions (LLxwxhh) 40x40x20

Power

Total power loss under IN 150 mW

Power dissipation per coil 150 mW

Materials

Surface appearance matt

Fluorescent bulbs control

Max. power fluo. duo lamp comp. series 40W

Incandescent bulbs control

Max. power with incandescent lamps 600 W

Connection

Type of contacts 1NO

Type of connection with screw-in lift terminals

Use conditions

Operating temperature -10...50 °C