



TU402



2-channel remote control

Technical characteristics

Architecture

| | |
|----------------|---|
| Number of keys | 2 |
|----------------|---|

Functions

| | |
|----------|--|
| Function | easy additional functions: +6 scenes, on/off operating mode, 1 up/down button control, reset function (to factory setting) |
|----------|--|

Dimensions

| | |
|-----------------------------|---------------------|
| Depth of installed product | 15.8 mm |
| Height of installed product | 83 mm |
| Dimensions (LLxwwxhh) | 83 x 46,5 x 15,8 mm |
| Width of installed product | 46.5 mm |

Safety

| | |
|---------------------|------|
| Protection index IP | IP50 |
|---------------------|------|

Use conditions

| | |
|-----------------------|-------------|
| Operating temperature | -10...45 °C |
|-----------------------|-------------|