




TU404



IP50



4-channel remote control

Technical characteristics

Dimensions

Depth of installed product	15.8 mm
Height of installed product	83 mm
Dimensions (LLxwwxhh)	83 x 46,5 x 15,8 mm
Width of installed product	46.5 mm

Safety

Protection index IP	IP50
---------------------	------

Use conditions

Operating temperature	-10...45 °C
-----------------------	-------------