




TU404



4-channel remote control

Technical characteristics

Architecture

Number of keys 4

Functions

Function easy additional functions: +6 scenes, on/off operating mode, 1 up/down button control ; reset function (to factory setting)

Dimensions

Depth of installed product 15.8 mm

Height of installed product 83 mm

Dimensions (LLxwwxhh) 83 x 46,5 x 15,8 mm

Width of installed product 46.5 mm

Reach distance

Max. transmission range 30m in house / 100m free field

Use conditions

Operating temperature -10...45 °C