




TU406



## 6-channel remote control

### Technical characteristics

#### Architecture

Number of keys 6

#### Functions

Function easy additional functions: +6 scenes, on/off operating mode, 1 up/down button control ; reset function (to factory setting)

#### Dimensions

Depth of installed product 16 mm

Height of installed product 133.6 mm

Dimensions (LLxwwxhh) 133,6 x 50,2 x 16 mm

Width of installed product 50.2 mm

#### Reach distance

Max. transmission range 30m in house / 100m free field

#### Use conditions

Operating temperature 0...45 °C