





TU418



18-channel remote control

Technical characteristics

Functions

Function	easy additional functions: +6 scenes, on/off operating mode, 1 up/down button control ; reset function (to factory setting)
----------	---

Dimensions

Depth of installed product	16 mm
Height of installed product	133.6 mm
Dimensions (LLxwxhh)	133,6 x 50,2 x 16 mm
Width of installed product	50.2 mm

Reach distance

Max. transmission range	30m in house / 100m free field
-------------------------	--------------------------------

Equipment

Switches / socket outlets	with channel group slide switch
---------------------------	---------------------------------

Use conditions

Operating temperature	0...45 °C
-----------------------	-----------