



TXA022

Weekly time switch EASY, 2 modules

Technical characteristics

Connectivity

| | |
|---------------------------|----|
| Bus system radio frequent | No |
|---------------------------|----|

Electric current

| | |
|-----------------|------|
| Bus consumption | 4 mA |
|-----------------|------|

Dimensions

| | |
|----------------------------|-------|
| Depth of installed product | 97 mm |
|----------------------------|-------|

| | |
|-----------------------------|-------|
| Height of installed product | 85 mm |
|-----------------------------|-------|

| | |
|----------------------------|-------|
| Width of installed product | 36 mm |
|----------------------------|-------|

Power

| | |
|---------------------------|-------|
| Total power loss under IN | 0.3 W |
|---------------------------|-------|

| | |
|----------------------------|-----|
| Dissipated energy in cable | 1 W |
|----------------------------|-----|

Materials

| | |
|------------|-----------------------|
| RAL colour | RAL 7035 - Light grey |
|------------|-----------------------|

Connection

| | |
|--------------------|----------------------|
| Type of connection | with screw terminals |
|--------------------|----------------------|

Settings

| | |
|-----------------------------|-----------|
| Summer / Winter time change | automatic |
|-----------------------------|-----------|

| | |
|-------------------------|------|
| Shortest switching time | 1 mn |
|-------------------------|------|

| | |
|---------------------|---------|
| Type of programming | digital |
|---------------------|---------|

Equipment

| | |
|--------------------|---|
| Number of channels | 2 |
|--------------------|---|

| | |
|------------------------|-----------------|
| Supply failure reserve | lithium battery |
|------------------------|-----------------|

Use

| | |
|-------|--------|
| Cycle | weekly |
|-------|--------|

Safety

| | |
|---------------------|------|
| Protection index IP | IP20 |
|---------------------|------|

Use conditions

| | |
|-----------------------|-----------|
| Operating temperature | 0...45 °C |
|-----------------------|-----------|