



TXA111



**Power supply 30V DC 320 mA**

**Technical Characteristics**

Bus system	EIB
Fixing mode	Din-Rail
Frequency	50/60 Hz
Supply voltage	230V AC
Fuse	with electronic short-circuit and overload protection
Depth of installed product	64 mm
Height of installed product	90 mm
Length	64 mm
Width of installed product	72 mm
Total power loss under IN	15 W
Number of modules	4
Colour	stone grey
RAL colour	RAL 7035 - Light grey
Connection cross-sect. flexible conductor	0,75 / 2,5mm <sup>2</sup>
Connection cross-sect. rigid cable	0,75 / 2.5mm <sup>2</sup>
Type of connection	quick connect
Type of connection	with QuickConnect plug-in terminals
Protection index IP	IP20
Operating temperature	-5...45 °C