



TXA204A

Output 4 -fold 4A

Technical characteristics

Architecture

Fixing mode	Din-Rail
-------------	----------

Controls and indicators

Indicator lamp	yes
----------------	-----

Connectivity

Bus system radio frequent	No
---------------------------	----

Main electrical features

Rated operational voltage Ue	207 / 230 / 264 V
------------------------------	-------------------

Power

Max. power with electronic transfo.	800 W
Total power loss under IN	1 W

Materials

Colour	stone grey
--------	------------

Fluorescent bulbs control

Max. power fluo. duo lamp comp. series	12 x 36 W
--	-----------

Incandescent bulbs control

Max. power with incandescent lamps	800 W
------------------------------------	-------

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	0...45 °C
-----------------------	-----------