



TXA204A

Output 4 -fold 4A

Technical characteristics

Architecture

Fixing mode	Din-Rail
-------------	----------

Controls and indicators

Indicator lamp	yes
----------------	-----

Connectivity

Bus system radio frequent	No
---------------------------	----

Main electrical features

Rated operational voltage Ue	207 / 230 / 264 V
------------------------------	-------------------

Power

Max. power with electronic transfo.	800 W
Total power loss under IN	1 W

Materials

Colour	stone grey
--------	------------

Incandescent bulbs control

Max. power with incandescent lamps	800 W
------------------------------------	-------

Connection

Connection cross-sect. flexible conductor	0,75 / 2,5mm ²
Connection cross-sect. rigid cable	0,75 / 2.5mm ²
Type of connection	quick connect

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	0...45 °C
-----------------------	-----------