



TXA204C

Output 4 -fold 16A

Technical characteristics

Architecture

Bus system EIB

Controls and indicators

Indicator lamp yes

Connectivity

Bus system radio frequent No

Main electrical features

Rated operational voltage U_e 207 / 230 / 264 V

Power

Max. power with electronic transfo. 1200 W

Total power loss under IN 3 W

Materials

Colour stone grey

Fluorescent bulbs control

Max. power fluo. duo lamp comp. series 20 x 36 W

Incandescent bulbs control

Max. power with incandescent lamps 2300 W

Safety

Protection index IP IP20

Use conditions

Operating temperature 0...45 °C