



TXA206A

Output 6 -fold 4A

Technical characteristics

Architecture

Fixing mode Din-Rail

Controls and indicators

Indicator lamp yes

Connectivity

Bus system radio frequent No

Main electrical features

Rated operational voltage U_e 230 V

Power

Max. power with electronic transfo. 800 W

Total power loss under IN 1 W

Materials

Colour stone grey

Fluorescent bulbs control

Max. power fluo. duo lamp comp. series 12 x 36 W

Incandescent bulbs control

Max. power with incandescent lamps 800 W

Safety

Protection index IP IP20

Use conditions

Operating temperature 0...45 °C