



TXA206B

Output 6 -fold 10A

Technical characteristics

Architecture

Bus system EIB

Controls and indicators

Indicator lamp yes

Connectivity

Bus system radio frequent No

Main electrical features

Rated operational voltage U_e 230 V

Power

Max. power with electronic transfo. 1000 W

Total power loss under IN 5 W

Fluorescent bulbs control

Max. power fluo. duo lamp comp. series 15 x 36 W

Incandescent bulbs control

Max. power with incandescent lamps 1200 W

Connection

Connection cross-sect. flexible conductor 0,75 / 2,5mm²

Connection cross-sect. rigid cable 0,75 / 2.5mm²

Type of connection quick connect

Type of contacts 6NO

Use conditions

Operating temperature 0...45 °C