



TXA206B

**Output 6 -fold 10A**

**Technical characteristics**

**Architecture**

Bus system EIB

**Controls and indicators**

Indicator lamp yes

**Connectivity**

Bus system radio frequent No

**Main electrical features**

Rated operational voltage  $U_e$  230 V

**Power**

Max. power with electronic transfo. 1000 W

Total power loss under IN 5 W

**Fluorescent bulbs control**

Max. power fluo. duo lamp comp. series 15 x 36 W

**Incandescent bulbs control**

Max. power with incandescent lamps 1200 W

**Connection**

Connection cross-sect. flexible conductor 0,75 / 2,5mm<sup>2</sup>

Connection cross-sect. rigid cable 0,75 / 2.5mm<sup>2</sup>

Type of contacts 6NO

**Use conditions**

Operating temperature 0...45 °C