



TXA206B

## Output 6 -fold 10A

### Technical characteristics

#### Architecture

|            |     |
|------------|-----|
| Bus system | EIB |
|------------|-----|

#### Controls and indicators

|                |     |
|----------------|-----|
| Indicator lamp | yes |
|----------------|-----|

#### Connectivity

|                           |    |
|---------------------------|----|
| Bus system radio frequent | No |
|---------------------------|----|

#### Main electrical features

|                                 |       |
|---------------------------------|-------|
| Rated operational voltage $U_e$ | 230 V |
|---------------------------------|-------|

#### Power

|                                     |        |
|-------------------------------------|--------|
| Max. power with electronic transfo. | 1000 W |
|-------------------------------------|--------|

|                           |     |
|---------------------------|-----|
| Total power loss under IN | 5 W |
|---------------------------|-----|

#### Fluorescent bulbs control

|  |           |
|--|-----------|
| Max. power fluo. duo lamp comp. series | 15 x 36 W |
|--|-----------|

#### Incandescent bulbs control

|                                    |        |
|------------------------------------|--------|
| Max. power with incandescent lamps | 1200 W |
|------------------------------------|--------|

#### Connection

|   |                           |
|---|---------------------------|
| Connection cross-sect. flexible conductor | 0,75 / 2,5mm <sup>2</sup> |
|---|---------------------------|

|                                    |                           |
|------------------------------------|---------------------------|
| Connection cross-sect. rigid cable | 0,75 / 2.5mm <sup>2</sup> |
|------------------------------------|---------------------------|

|                    |               |
|--------------------|---------------|
| Type of connection | quick connect |
|--------------------|---------------|

|                  |     |
|------------------|-----|
| Type of contacts | 6NO |
|------------------|-----|

#### Use conditions

|                       |           |
|-----------------------|-----------|
| Operating temperature | 0...45 °C |
|-----------------------|-----------|