



TXA206B



Output 6 -fold 10A

Technical Characteristics

| | |
|---|---------------------------|
| Bus system | EIB |
| Fixing mode | Din-Rail |
| Indicator lamp | yes |
| Bus system radio frequent | No |
| Rated operational voltage Ue | 230 V |
| Rated current | 10 A |
| Max. power with electronic transfo. | 1000 W |
| Total power loss under IN | 5 W |
| Breaking capacity | AC1 |
| Number of modules | 4 |
| Colour | stone grey |
| Max. power fluo. duo lamp comp. series | 15 x 36 W |
| Max. power with incandescent lamps | 1200 W |
| Connection cross-sect. flexible conductor | 0,75 / 2,5mm ² |
| Connection cross-sect. rigid cable | 0,75 / 2.5mm ² |
| Type of connection | quick connect |
| Type of contacts | 6NO |
| Protection index IP | IP20 |
| Operating temperature | 0...45 °C |