



TXA206B

## Output 6 -fold 10A

### Technical characteristics

#### Architecture

Bus system	EIB
------------	-----

#### Controls and indicators

Indicator lamp	yes
----------------	-----

#### Connectivity

Bus system radio frequent	No
---------------------------	----

#### Main electrical features

Rated operational voltage Ue	230 V
------------------------------	-------

#### Power

Max. power with electronic transfo.	1000 W
-------------------------------------	--------

Total power loss under IN	5 W
---------------------------	-----

#### Materials

Colour	stone grey
--------	------------

#### Fluorescent bulbs control

Max. power fluo. duo lamp comp. series	15 x 36 W
--	-----------

#### Incandescent bulbs control

Max. power with incandescent lamps	1200 W
------------------------------------	--------

#### Connection

Type of connection	quick connect
--------------------	---------------

#### Safety

Protection index IP	IP20
---------------------	------

#### Use conditions

Operating temperature	0...45 °C
-----------------------	-----------