



TXA206C

Output 6 -fold 16A

Technical characteristics

Architecture

Bus system	EIB
------------	-----

Controls and indicators

Indicator lamp	yes
----------------	-----

Connectivity

Bus system radio frequent	No
---------------------------	----

Main electrical features

Rated operational voltage U_e	230 V
---------------------------------	-------

Power

Max. power with electronic transfo.	1200 W
-------------------------------------	--------

Total power loss under IN	12 W
---------------------------	------

Fluorescent bulbs control

Max. power fluo. duo lamp comp. series	20 x 36 W
--	-----------

Incandescent bulbs control

Max. power with incandescent lamps	2300 W
------------------------------------	--------

Connection

Connection cross-sect. flexible conductor	0,75 / 2,5mm ²
---	---------------------------

Connection cross-sect. rigid cable	0,75 / 2.5mm ²
------------------------------------	---------------------------

Type of contacts	6NO
------------------	-----

Use conditions

Operating temperature	0...45 °C
-----------------------	-----------