



TXA206D



Output 6 -fold 16A C-Load adapted

Technical characteristics

Architecture

Bus system KNX

Controls and indicators

Indicator lamp yes

Connectivity

Bus system radio frequent No

Main electrical features

Rated operational voltage U_e 230 V

Dimensions

Height 90 mm

Power

Max. power with electronic transfo. 1200 W

Total power loss under IN 12 W

Fluorescent bulbs control

Max. power fluo. duo lamp comp. series 1500W - 200 μ F

Incandescent bulbs control

Max. power with incandescent lamps 2300 W

Connection

Connection cross-sect. flexible conductor 0,75 / 2,5mm²

Connection cross-sect. rigid cable 0,75 / 2.5mm²

Type of load C-Load

Type of contacts 6NO

Type of connection with QuickConnect plug-in terminals

Use conditions

Operating temperature 0...45 °C