



TXA206D



IP30



Output 6 -fold 16A C-Load adapted

Technical Characteristics

Bus system	KNX
Fixing mode	REG
Indicator lamp	yes
Rated operational voltage Ue	230 V
Frequency	50/60 Hz
Rated current	16 A
Height	90 mm
Max. power with electronic transfo.	1200 W
Total power loss under I _N	12 W
Breaking capacity	16A 250V AC1
Number of modules	4
Colour	light grey
Max. power fluo. duo lamp comp. series	1500W - 200µF
Max. power with incandescent lamps	2300 W
Connection cross-sect. flexible conductor	0,75 / 2,5mm ²
Connection cross-sect. rigid cable	0,75 / 2.5mm ²
Type of load	C-Load
Type of connection	quick connect
Type of contacts	6NO
Type of connection	with QuickConnect plug-in terminals
Protection index IP	IP30
Operating temperature	0...45 °C