



TXA206D

IP30



Output 6 -fold 16A C-Load adapted

Technical characteristics

Architecture

Bus system	KNX
------------	-----

Controls and indicators

Indicator lamp	yes
----------------	-----

Connectivity

Bus system radio frequent	No
---------------------------	----

Main electrical features

Rated operational voltage Ue	230 V
Frequency	50/60 Hz

Dimensions

Height	90 mm
--------	-------

Power

Max. power with electronic transfo.	1200 W
Total power loss under IN	12 W

Materials

Colour	light grey
--------	------------

Fluorescent bulbs control

Max. power fluo. duo lamp comp. series	1500W - 200μF
--	---------------

Incandescent bulbs control

Max. power with incandescent lamps	2300 W
------------------------------------	--------

Connection

Type of connection	quick connect
--------------------	---------------

Use conditions

Operating temperature	0...45 °C
-----------------------	-----------